

Stainless Steel Multi-Branch Manifold



Features

- **Quick-assembly and disassembly**
Each component can be easily removed for cleaning and autoclaving .
- **SS316 Stainless Steel**
All wetted parts of MultiVac 300 / 600 manifold are made of SS316 stainless steel, which is more durable.
- **Quick-Fit hose barb**
Detachable hose barb can be connected to either side of the manifold quickly towards the vacuum source.
- **Innovative vent valve design**
An adjustable vent valve integrated with the pipe can eliminate water hammer phenomenon and help drain out residual waste water.
- **Individual control valve**
Each branch permits individual control.
- **Compatible with different kinds of filter holders**
MultiVac 300 / 600 - MS manifold includes No.8 silicone stoppers which can accept various types of filter holders at option.

Applications

- Microbiological test
- Suspended solid test
- Vacuum filtration

Ordering Information

180300-01

MultiVac 300 - MS, 3 Places SS Manifold with No. 8 stopper funnel adaptor

180600-01

MultiVac 600 - MS, 6 Places SS Manifold with No. 8 stopper funnel adaptor

200300-01

MF 3, 300 ml Magnetic Filter Holder with lid kit

167110-16

No.8 Silicone Stopper

MultiVac 300 - MS



Adjustable vent valve



Quick-Fit hose barb

MultiVac 600 - MS



Specification

Model	MultiVac 300 - MS	MultiVac 600 - MS
Number of branch	3	6
Filter diameter	Optional	Optional
Funnel capacity	Optional	Optional
Hose barb	ID8	ID8
Dimension (LxWxH)	48 x 13 x 16 cm	85 x 13 x 16 cm
Part	Material	Material
Body	SS316	SS316
Control valve	SS316	SS316
Adaptor	SS316	SS316
Hose barb / Vent valve	SS316	SS316
Handle / Knob	Aluminum	Aluminum

Stainless Steel Spin-Lock Design Multi-Branch Manifold



Features

- ▶ **Quick-assembly and disassembly**
Each component can be easily removed for cleaning and autoclaving .
- ▶ **SS316 Stainless Steel**
All wetted parts of MultiVac 300 / 600 manifold are made of SS316 stainless steel, which is more durable.
- ▶ **Quick-Fit hose barb**
Detachable hose barb can be connected to either side of the manifold quickly towards the vacuum source.
- ▶ **Innovative vent valve design**
An adjustable vent valve integrated with the pipe can eliminate water hammer phenomenon and help drain out residual waste water.
- ▶ **Individual control valve**
Each branch permits individual control.
- ▶ **Compatible with different sizes of funnels**
MultiVac 300 / 600 - MB manifolds can accept Rocker SF stainless steel funnel - 100 / 300 / 500 ml at option.

Applications

- ▶ Microbiological test
- ▶ Suspended solid test
- ▶ Vacuum filtration

Ordering Information

- 180300-02**
MultiVac 300 - MB, 3 Places SS Manifold with Rocker SF funnel adaptor
- 180600-02**
MultiVac 600 - MB, 6 Places SS Manifold with Rocker SF funnel adaptor
- 180100-01**
SF, 100 ml Stainless Steel Funnel
- 180100-03**
SF, 300 ml Stainless Steel Funnel
- 180100-05**
SF, 500 ml Stainless Steel Funnel

MultiVac 300 - MB



Adjustable vent valve



Quick-Fit hose barb

MultiVac 600 - MB



Specification

Model	MultiVac 300 - MB	MultiVac 600 - MB
Number of branch	3	6
Filter diameter	47 mm	47 mm
Funnel capacity	100 ml / 300 ml / 500 ml (optional)	100 ml / 300 ml / 500 ml (optional)
Hose barb	ID8	ID8
Dimension (LxWxH)	48 x 13 x 11 cm	85 x 13 x 11 cm
Part	Material	Material
Body	SS316	SS316
Control valve	SS316	SS316
Adaptor	SS316	SS316
Membrane support	SS316	SS316
Hose barb / Vent valve	SS316	SS316
Handle / Knob	Aluminum	Aluminum

How to order?

You can select Combination A, B or C

A

Step 1. Choose the manifold



MultiVac 300 - MB
3 Places Stainless Steel Manifold
(180300-02)



MultiVac 600 - MB
6 Places Stainless Steel Manifold
(180600-02)



Step 2. Choose the SF funnel



Rocker, 100 ml
SF Stainless Steel Funnel
(180100-01)



Rocker, 300 ml
SF Stainless Steel Funnel
(180100-03)



Rocker, 500 ml
SF Stainless Steel Funnel
(180100-05)



Stainless Steel Cover
for SF 100 ml funnel
(180100-11)



Stainless Steel Cover
for SF 300 ml / 500 ml funnel
(180100-13)

B

Step 1. Choose the manifold



MultiVac 300 - MS
3 Places Stainless Steel Manifold
(180300-01)



MultiVac 600 - MS
6 Places Stainless Steel Manifold
(180600-01)



Step 2. Choose the filter holder



Rocker, 300 ml
MF 3, Magnetic Filter Holder
(200300-01)



Rocker, 500 ml
MF 5, Magnetic Filter Holder
(200500-01)



Rocker, 300 ml
VF 6, Glass Filter Holder
(167120-31)

to complete your order



Step 1. Choose the manifold



MultiVac 300
3 Places Stainless Steel Manifold Base
(180300-00)



MultiVac 600
6 Places Stainless Steel Manifold Base
(180600-00)



Step 2. Choose the disposable funnel and adaptor



Sartorius, 100 ml / 250 ml
Microart® disposable plastic funnel
(16A07--10-----N/
16A07--25-----N)



Millipore, 100 ml / 250 ml
Microfil® disposable plastic funnel
(MIHAWG100 / MIHAWG250)



Pall, 100 ml / 250 ml
Sentino® disposable plastic funnel
(4870 / 4871)



SS316 Adaptor for Sartorius
disposable plastic funnel
(190100-74)



SS316 Adaptor for Millipore
disposable plastic funnel
(190100-73)




SS316 Adaptor for Pall
disposable plastic funnel
(190100-75)

* SS316 adaptor is only available for above-mentioned disposable funnels.

Customized Design

We can offer customized adaptor for your funnel



Votre revendeur :



42 à 48 bd de Polangis - BP 260
94502 Champigny-sur-Marne - Cedex
☎ 01 48 83 21 76 - 📠 01 48 83 51 01
info@cloup.fr www.cloup.fr